

Certificate of compliance

with the order 2.1 according to EN 10 204

HELUPOWER[®] SJOOW

We confirm that the above mentioned **Rubber control and connection cable** is produced and tested **acc. to UL-Std. 62, CSA-Std. C22.2 No. 49.**

TECHNICAL DATA

Temperature range	flexible -20°C to +90°C fixed -40°C to +90°C
Permissible operating temperature of the conductor	+90°C
Nominal voltage	AC U 300 V

TESTS

flame-retardant acc. to CSA FT2
certifications and approvals:
Mine Safety and Health Administration (MSHA), U.S. Department of Labor
for Class 1 Div. 2 explosive environments acc. to NEC Art. 501

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
20.06.2023

Date of expiration
31.12.2024

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrasse 10
71282 Hemmingen
Germany