

Certificate of compliance

with the order 2.1 according to EN 10 204

MULTIFLEX 512[®]-PUR

We confirm that the above mentioned **PUR drag chain cable** is produced **in alignment with DIN VDE 0285-525-2-21 / DIN EN 50525-2-21** and tested according to DIN EN 50395, DIN EN 50396.

TECHNICAL DATA

Temperature range	flexible -30°C to +80°C fixed -40°C to +80°C
Nominal voltage	AC U ₀ /U 300/500 V

TESTS

oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404

UV-resistant acc. to DIN EN ISO 4892-2

weather-resistant acc. to DIN EN ISO 4892-2

Alternate bending test: tested on approx. 10 million cycles

certifications and approvals:

EAC

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
26.09.2022

Date of expiration
31.12.2023

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany