

# Certificate of compliance

with the order 2.1 according to EN 10 204

## TOPFLEX®-EMV-UV-3-PLUS-2XSLCYK-J UL/CSA

We confirm that the above mentioned **Motor connection cable for frequency converters** is produced **acc. to UL-Std. 758 (AWM) Style 21179, in alignment with DIN VDE 0250** and tested according to DIN EN 50395, DIN EN 50396.

### TECHNICAL DATA

<b>Temperature range</b>	flexible -5°C to +90°C fixed -40°C to +90°C
<b>Permissible operating temperature of the conductor</b>	+90°C
<b>Nominal voltage</b>	UL (AWM) AC 1000 V

### TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, CSA FT1  
electromagnetic compatibility acc. to DIN VDE 0875-11 / DIN EN 55011

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
15.01.2024

**Date of expiration**  
31.12.2025

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany