

# Certificate of compliance

with the order 2.1 according to EN 10 204

## SiHF UL/CSA

We confirm that the above mentioned **Silicone control and connection cable** is produced **acc. to UL-Std. 758 (AWM) Style 4476, CSA-Std. C22.2 No. 210 - AWM I/II A/B** and tested according to DIN EN 50395, DIN EN 50396.

## TECHNICAL DATA

<b>Temperature range</b>	VDE -60°C to +180°C UL (AWM) -50°C to +150°C
<b>Nominal voltage</b>	VDE AC U <sub>0</sub> /U 300/500 V UL (AWM) AC 600 V

## TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1  
corrosiveness of combustion gases acc. to DIN VDE 0482-754-2 / DIN EN 60754-2 / IEC 60754-2  
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2, CSA FT1  
certifications and approvals:  
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
15.01.2024

**Date of expiration**  
31.12.2025

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany