

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

NSHTÖU

We confirm that the above mentioned Special-crane-drum cables are produced according to DIN VDE 0250 part 814 and tested according to EN 50396, EN 50395.

- **Temperature range**
 - flexing - 25°C to + 70°C
 - fixed installation - 40°C to + 70°C
- **max. temperature at conductor**
 - in operation + 60°C
 - in short-circuit + 200°C
- **Nominal voltage** U₀/U 0,6/1 kV

Tests

- Behaviour in fire according to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2.
- Oil resistant according to DIN VDE 0473-811-404, DIN EN 60811-404.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam