

Certificate of compliance

with the order 2.1 according to EN 10 204

NA2XS2Y

We confirm that the above mentioned **Medium voltage cable** is produced **acc. to DIN VDE 0276-620, HD 620 S2, IEC 60502** and tested according to HD 620.

TECHNICAL DATA

Temperature range	during installation -20°C
Permissible operating temperature of the conductor	+90°C
Short circuit temperature at the conductor	+250°C (Short circuit duration max. 5 s)
Nominal voltage	U ₀ /U 6/10kV, 12/20 kV, 18/30 kV
Operating voltage	for 6/10 kV = U max. 12 kV for 12/20 kV = U max. 24 kV for 18/30 kV = U max. 36 kV

PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

HELU KABEL GmbH
Technical Department

This document is valid without signature

Date of issue
14.09.2023

Date of expiration
31.12.2025

Point of Contact
Christian Dettmer
Tel. +49 7150 9209-712
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH
Headquarters
Schloßhaldenstrabe 10
71282 Hemmingen
Germany