

HELU KABEL GmbH  
Headquarters  
Dieselstraße 8-12  
71282 Hemmingen  
Germany

P +49 7150 9209-0  
F +49 7150 81786  
techsupport@helukabel.de  
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance  
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

**J-H(St)H**

We confirm that above mentioned flame retardant, halogen-free Installation cable are produced and tested according to DIN VDE 0815.

- **Temperature range**
  - flexing - 5°C to + 50°C
  - fixed installation - 30°C to + 70°C
- **Operating peak voltage** 300V  
(not for purposes of high current and power installation)

**Tests**

- Flame-test according to DIN VDE 0482-332-3-24, DIN EN 60332-3-24, IEC 60332-3-24.
- Corrosiveness of combustion gases according to DIN VDE 0482-754-2, DIN EN 60754-2, IEC 60754-2.
- Smoke density according to DIN VDE 0482-1034-1+2, DIN EN 61034-1+2, IEC 61034-1+2.

The materials used in manufacture are cadmium-free and contain no silicone and free from substances harmful to the wetting properties of lacquers.

**CE** = Product conforms with Low-Voltage Directive 2014/35/EU.

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands  
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam