

# Certificate of compliance

with the order 2.1 according to EN 10 204

## H07RN-F / 07RN-F

We confirm that the above mentioned **Rubber connection cable** is produced: **H07RN-F acc. to DIN VDE 0285-525-2-21 / DIN EN 50525-2-21; 07RN-F in alignment with DIN VDE 0285-525-2-21 / DIN EN 50525-2-21** and tested according to DIN EN 50395, DIN EN 50396.

## TECHNICAL DATA

<b>Temperature range</b>	flexible -25°C to +60°C fixed -30°C to +60°C
<b>Permissible operating temperature of the conductor</b>	+60°C
<b>Nominal voltage</b>	AC U <sub>0</sub> /U 450/750 V

## TESTS

flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2  
oil-resistant acc. to DIN VDE 0473-811-404 / DIN EN 60811-404 / IEC 60811-404  
certifications and approvals:  
H07RN-F: HAR  
EAC



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
25.09.2023

**Date of expiration**  
31.12.2025

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany