

HELU KABEL GmbH
Headquarters
Schloßhaldenstraße 10
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

HELU KABEL GmbH • Schloßhaldenstraße 10 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	19.10.2022	31.12.2023

TUBEFLEX-(St)-CY

We confirm that the above mentioned PVC cable is produced acc. to company standard and tested according to DIN EN 50395, DIN EN 50396.

- **Temperature range** - 20°C up to + 80°C
- **Voltage rating** max. 300 V

Test

- flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Norway • Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam

Managing Director: Helmut Luksch, Marc Luksch, Andreas Hoppe
Registered Office: Hemmingen, Germany
District Court: Stuttgart HRB 201352
VAT-Id DE 146 021 824 · Tax number 70074/03759
EORI number DE 2623064 · AEO DE AEOF 108137 · WEEE-Reg. number DE 23651005

Baden-Württembergische Bank
Commerzbank AG
Deutsche Bank AG
HSBC Trinkaus & Burkhardt AG
Kreissparkasse Ludwigsburg

SWIFT/BIC SOLADEST600
SWIFT/BIC COBADEFFXXX
SWIFT/BIC DEUTDE55XXX
SWIFT/BIC TUBDDEDDXXX
SWIFT/BIC SOLADES1LBG

IBAN DE18 6005 0101 7832 5010 24
IBAN DE41 6004 0071 0830 7522 00
IBAN DE21 6007 0070 0987 6160 00
IBAN DE77 3003 0880 0500 3320 18
IBAN DE46 6045 0050 0030 1165 55