

# Certificate of compliance

with the order 2.1 according to EN 10 204

## HELUKABEL<sup>®</sup> SINGLE CORE UL Style 1015

We confirm that the above mentioned **PVC single core** is produced and tested **acc. to UL-Std. 758 (AWM) Style 1015, CSA-Std. C22.2 No. 210 - AWM I A/B, 24 AWG - 4/0 AWG: CSA-Std. C22.2 No. 127 - TEW, 22 AWG - 500 kcmil: UL-Std. 1063 (MTW).**

### TECHNICAL DATA

<b>Temperature range</b>	flexible -5°C to +105°C fixed -40°C to +105°C
<b>Nominal voltage</b>	UL (AWM) AC 600 V UL (MTW) AC 600 V CSA (TEW) AC 600 V

### TESTS

flame-retardant acc. to UL VW-1, CSA FT1

### PROPERTIES

the materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

---

**Date of issue**  
01.12.2022

**Date of expiration**  
31.12.2023

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany