

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

TRAYCONTROL® 300 TP

We confirm that the above mentioned PVC cables, NFPA 79, are produced according to UL-Std. 13 (PLTC-ER / AWG 22-AWG 16), UL-Std. 444 (CM), AWM Style 2517, CSA CMG.

- **Temperature range** - 25°C to + 105°C
- **Nominal voltage** 300 V

Approvals:

- **UL (AWG 22 - AWG 18)**
PLTC-ER, ITC-ER, Type CM, OIL RES I & II,
Class I Div. 2, NEC Art. 501, 725, 760 & 800, AWM 2517
- **UL (AWG 24 - AWG 26)**
CM, AWM 2517, rated OIL RES I & II, NEC Art. 725, 760 & 800
- **CSA**
CSA CMG FT4, AWM I/II A/B FT4

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam