

HELU KABEL GmbH
Headquarters
Dieselstraße 8-12
71282 Hemmingen
Germany

P +49 7150 9209-0
F +49 7150 81786
techsupport@helukabel.de
helukabel.com

Helukabel GmbH • Dieselstraße 8-12 • 71282 Hemmingen • Germany

**Certificate of compliance
with the order 2.1 according to EN 10 204**

Telephone, Name	Date	Effective date
-712, C. Dettmer	01.06.2021	31.07.2022

JZ 604-FCY TC TRAY CABLE

We confirm that the above mentioned, screened PVC cables, NFPA 79, are produced according to UL-Std. 1277 TRAY CABLE.

- **Multinorm**
TRAY-CABLE also conforms to the following standards:
AWM-Style 2587 to UL-Std. 758 and CSA C22.2 No 210 I/II A/B 90°C 600 V
- **Temperature range**
dry environment
flexing - 5°C to + 90°C
fixed installation - 25°C to + 90°C

wet environment
flexing - 5°C to + 75°C
fixed installation - 25°C to + 75°C
- **Nominal voltage** UL 600 V

Test

- Material self-extinguishing and flame retardant to CSA FT 4.

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELU KABEL GmbH
Technical Department

This document is valid without signature



Austria • Belgium • Brazil • Bulgaria • Canada • China • Czech Republic • Denmark • Finland • France • Germany • Hungary • India • Indonesia • Italy • Malaysia • Mexico • Myanmar • Netherlands
Peru • Poland • Portugal • Romania • Russia • Singapore • South Africa • South Korea • Spain • Sweden • Switzerland • United Arab Emirates • United Kingdom • USA • Thailand • Turkey • Vietnam