

# Certificate of compliance

with the order 2.1 according to EN 10 204

## SOLARFLEX®-X H1Z2Z2-K NTS

We confirm that the above mentioned **Cross-linked single core cable** is produced **in alignment with DIN VDE 0283-618 / DIN EN 50618** and tested according to DIN EN 50395, DIN EN 50396.

### TECHNICAL DATA

|   |  |
|---|--|
| <b>Temperature range</b>                                  | fixed -40°C to +90°C   |
| <b>Permissible operating temperature of the conductor</b> | +120°C   |
| <b>Nominal voltage</b>                                    | AC U <sub>0</sub> /U 1000/1000 V<br>DC U <sub>0</sub> /U 1500/1500 V |

### TESTS

halogen-free acc. to DIN VDE 0482-754-1 / DIN EN 60754-1 / IEC 60754-1  
flame-retardant acc. to DIN VDE 0482-332-1-2 / DIN EN 60332-1-2 / IEC 60332-1-2  
smoke density acc. to DIN VDE 0482-1034-1+2 / DIN EN 61034-1+2 / IEC 61034-1+2  
UV-resistant acc. to DIN VDE 0283-618 / DIN EN 50618 Appendix E  
ozone-resistant acc. to DIN VDE 0283-618 / DIN EN 50618  
weather-resistant acc. to DIN VDE 0283-618 / DIN EN 50618 Appendix E  
DC Voltage resistance of the insulation acc. to DIN VDE 0283-618 / DIN EN 50618 Tab. 2



Product conforms with Low-Voltage Directive 2014/35/EU

**HELU KABEL GmbH**  
Technical Department

This document is valid without signature

**Date of issue**  
11.10.2022

**Date of expiration**  
31.12.2023

**Point of Contact**  
Christian Dettmer  
Tel. +49 7150 9209-712  
techsupport@helukabel.de  
helukabel.com

**HELU KABEL GmbH**  
Headquarters  
Schloßhaldenstraße 10  
71282 Hemmingen  
Germany